

TECHSPEC® 40mm Dia. x 450mm FL, VIS 0° Coated, Achromatic Lens



Stock **#49-282** 10 TO 12 DAYS
[Other Coating Options](#)

⊖ 1 ⊕ **₹14,616.00**

ADD TO CART

Qty 1-5
₹14,616.00
Qty 6+
₹11,702.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
450.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 445.69
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 39.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 6.00 ±0.10
Center Thickness CT 2 (mm) : 4.00 ±0.10
Radius R₁ (mm) : 279.60
Radius R₂ (mm) : -199.51
Radius R₃ (mm) : -579.39
Edge Thickness ET (mm) : 8.94
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 11.25
Numerical Aperture NA : 0.04
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View