

40mm Dia. x 200mm FL, MgF₂ Coated, DCX N-K5 Lens



Stock **#32-911** CLEARANCE 10 TO 12 DAYS

[Other Coating Options](#)

- 1 + **₹1,736.00**

ADD TO CART

Qty 1+
₹1,736.00

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
40.00 +0.00/-0.10

Effective Focal Length EFL (mm):
200.00 @587.6nm

Back Focal Length BFL (mm):
197.36

Coating:
MgF₂ (400-700nm)

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Substrate: ☐ N-K5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.10
Edge Thickness ET (mm): 6.07
Clear Aperture CA (mm): 39
f/#: 5.00
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm² @532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View