


TECHSPEC® 40mm Dia x -100mm FL Negative Doublet Lens MgF₂ Coated



Stock #63-765

10 TO 12 DAYS

-

1

+

₹15,008.00

ADD TO CART

Qty 1-5
₹15,008.00
Qty 6+
₹12,006.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

40.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-100.00

Focal Length Tolerance (%):

±1

Back Focal Length BFL (mm):

-104.33
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 39.00
Centering (arcmin): <1
Center Thickness CT (mm): 10.50 ±0.20
Center Thickness CT 1 (mm): 4.00 ±0.10
Center Thickness CT 2 (mm): 6.50 ±0.10
Radius R₁ (mm): -60.11
Radius R₂ (mm): 48.43
Radius R₃ (mm): 149.50
Edge Thickness ET (mm): 15.08
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View