

[See all 24 Products in Family](#)

TECHSPEC® 40mm Dia x -60mm FL Negative Doublet Lens MgF₂ Coated



Stock **#63-763** **20+ In Stock**

- 1 + MRP ₹20,178

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,178 each
Qty 6-25	₹16,142 each
Qty 26-49	₹15,134 each
Need More?	Request Quote

Product Downloads

General

Negative Achromatic Lens **Type:**

Physical & Mechanical Properties

40.00 +0.0/-0.025 **Diameter (mm):**

39.00 **Clear Aperture CA (mm):**

<1	Centering (arcmin):
13.50 ±0.20	Center Thickness CT (mm):
5.00 ±0.10	Center Thickness CT 1 (mm):
8.50 ±0.10	Center Thickness CT 2 (mm):
19.02	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties

-60.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
-67.12	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
-41.26	Radius R₁ (mm):
30.56	Radius R₂ (mm):
335.88	Radius R₃ (mm):
N-BAF10 / N-SF10	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
1.5	f/#:
0.33	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @400 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 700	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Magnesium Fluoride (MgF_2) Coating
- Used to Extend Focal Length
- [Broadband AR Coated Negative Achromatic Lenses](#) Also Available

TECHSPEC® MgF_2 Coated Negative Achromatic Lenses consist of two optical elements cemented together. Negative doublet lenses are corrected for color and on-axis aberrations. TECHSPEC MgF_2 Coated Negative Achromatic Lenses are used predominantly as Barlow lenses to extend focal lengths. These lenses are often combined with positive achromatic mirror systems and imaging lenses.

Technical Information



Coating Curves

Compatible Mounts