

[See all 102 Products in Family](#)

40mm Dia. x 29.5mm FL, Aspheric Condenser Lens



Stock #22-845 **14 In Stock**

[Other Coating Options](#)

1 MRP ₹7,213

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,213 each
Qty 11-49	₹6,558 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

40.00 +0.0/-0.2 **Diameter (mm):**

≤30 **Centering (arcmin):**

36.00	Clear Aperture CA (mm):
4.04	Edge Thickness ET (mm):
15.50 ±0.30	Center Thickness CT (mm):
Protective as needed	Bevel:
40.00	Diameter of Asphere (mm):
Convex	Shape of Back Surface:

Optical Properties

29.50	Effective Focal Length EFL (mm):
0.68	Numerical Aperture NA:
20.89	Back Focal Length BFL (mm):
H-K9L	Substrate: <input type="checkbox"/>
±8	Focal Length Tolerance (%):
Uncoated	Coating:
80-50 (typical)	Surface Quality:
0.74	f#:
67.75	Radius R₂ (mm):
Infinite	Conjugate Distance:

Regulatory Compliance

View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



