

TECHSPEC® 40mm Diameter, VIS-NIR Coated, Calcium Fluoride Window



TECHSPEC Calcium Fluoride (CaF2) Windows

Stock #14-820 **2 In Stock**

⊖ 1 ⊕ MRP ₹31,881

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹31,881 each
Qty 11-25	₹28,047 each
Qty 26-49	₹26,535 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

36.00	Diameter (mm):
40.00 +0.0/-0.1	
	Thickness (mm):
3.00 ±0.1	
	Parallelism (arcmin):
<1	
	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Edges:
Fine Ground	
	Poisson's Ratio:
0.26	
	Young's Modulus (GPa):
75.8	
	Knoop Hardness (kg/mm²):
158.30	

Optical Properties

	Coating:
VIS-NIR (400-1000nm)	
	Substrate: <input type="checkbox"/>
Calcium Fluoride (CaF ₂) Vacuum UV Grade	
	Index of Refraction (n_d):
1.434	
	Surface Quality:
40-20	
	Abbe Number (v_d):
94.99	
	Axis Orientation:
Random	
	Coating Specification:
R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm	
	Wavelength Range (nm):
400 - 1000	
	Surface Flatness (P-V):
λ/2	
	Damage Threshold, By Design: <input type="checkbox"/>
5 J/cm ² @ 532nm, 10ns	

Material Properties

	Density (g/cm³):
3.18	
	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
18.85	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 235:
Compliant	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness

- Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Low Absorption, High Transmission UV Grade Calcium Fluoride
- Low Index of Refraction
- AR Coatings Spanning 250 - 5000nm Available
- [Calcium Fluoride \(CaF₂\) Wedged Windows](#) also Available

TECHSPEC® Calcium Fluoride (CaF₂) Windows offer a low index of refraction, providing high transmission from 200 - 7000nm when used uncoated. To further increase transmission and reduce back reflections, a variety of AR coatings are available spanning wavelength regions from the Ultra-Violet (UV) to the Mid-Wave Infrared (MMIR). The high bulk damage threshold of calcium fluoride coupled with its low absorption makes it a popular choice for use with laser systems, including excimer lasers. TECHSPEC® Calcium Fluoride (CaF₂) Windows are ideal for use as protective windows for gas detectors operating in the Vacuum UV (VUV) and MMIR, UV spectroscopy systems, cryogenically cooled thermal imaging systems, and as substrates for coatings requiring wideband substrate transmission.

Note: Calcium fluoride is a relatively soft optical material and is more susceptible to scratches than typical glass windows. Calcium fluoride is also susceptible to thermal shock.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Coating Curves

Compatible Mounts