

40mm Diameter x 28.5mm FL, Aspheric Condenser Lens



Stock **#46-685** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹7,567

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-10	₹7,567 each
Qty 11-49	₹6,659 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

40.00 +0.2/-0.2 **Diameter (mm):**

≤25 **Centering (arcmin):**

34	Clear Aperture CA (mm):
2.0	Edge Thickness ET (mm):
15.00 ±0.25	Center Thickness CT (mm):
Protective as needed	Bevel:
36.0	Diameter of Asphere (mm):
Plano	Shape of Back Surface:

Optical Properties

28.50	Effective Focal Length EFL (mm):
0.63	Numerical Aperture NA:
18.7	Back Focal Length BFL (mm):
B270	Substrate: <input type="checkbox"/>
±7	Focal Length Tolerance (%):
Uncoated	Coating:
80-50 (typical)	Surface Quality:
0.8	f#:
58.5	Abbe Number (v_d):
1.523	Index of Refraction (n_d):
Plano	Radius R₂ (mm):
350 - 2500	Wavelength Range (nm):
Infinite	Conjugate Distance:

Material Properties

9.4	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
-----	---

Regulatory Compliance



Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



Compatible Mounts