


[See all 6 Products in Family](#)

**TECHSPEC® 4.0mm Diameter x 4.0mm Length, N-LASFN9 Half-Drum Lens**



Stock #46-531 CLEARANCE **1 In Stock**

1  MRP ₹2,447

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,447 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Half-Drum Lens **Type:**

**Physical & Mechanical Properties**

4.00 **Diameter (mm):**

4.00 **Length (mm):**

±30 **Length Tolerance (µm):**

2.50	<b>Radius R (mm):</b>
+0/-1.5	<b>Radius Tolerance (µm):</b>
+0/-50	<b>Diameter Tolerance (µm):</b>
<b>Optical Properties</b>	
<b>N-LASF9</b>	<b>Substrate:</b> <input type="checkbox"/>
Uncoated	<b>Coating:</b>
380 - 2500	<b>Wavelength Range (nm):</b>
1.850	<b>Index of Refraction (n<sub>d</sub>):</b>
40-20	<b>Surface Quality:</b>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Easier to Mount and Handle Than Standard Ball Lenses

Drum lenses are glass spheres, ground down axially to provide a mounting surface. The ground circumference D simplifies handling issues typically associated with ball lenses. Ideal for optical transmission in fiber communications. Type B Drum lenses have a polished plano-surface for direct fiber contact and perform as elongated PCX lenses.

## Technical Information

D	Radius R	Length	Length L2	Stock No.
<b>Type A Drum Lenses</b>				
2mm	1.25mm	2.5mm	1.5mm	<a href="#">#45-548</a>
				<a href="#">#45-739</a>
				<a href="#">#45-836</a>
				<a href="#">#45-663</a>
				<a href="#">#45-743</a>
2.4mm	1.5mm	3mm	1.8mm	<a href="#">#45-549</a>
				<a href="#">#45-837</a>
				<a href="#">#45-664</a>
				<a href="#">#45-744</a>
3.2mm	2mm	4mm	2.4mm	<a href="#">#45-550</a>
				<a href="#">#45-741</a>
				<a href="#">#45-838</a>
				<a href="#">#45-665</a>
				<a href="#">#45-745</a>
4mm	2.5mm	5mm	3mm	<a href="#">#45-551</a>
				<a href="#">#45-839</a>

				#45-742
				#45-666
<b>Type B Half-Drum Lenses</b>				
2mm	1.25mm	2mm	1.5mm	#46-524
				#46-528
2.4mm	1.5mm	2.4mm	1.8mm	#46-525
				#46-529
3.2mm	2mm	3.2mm	2.4mm	#46-526
				#46-530
4mm	2.5mm	4mm	3mm	#46-527
				#46-531

