

## 40mm Sq. English Kinematic Magnetic Base



Stock #22-407 **7 In Stock**

MRP ₹10,998

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹10,998 each
Qty 10+	₹9,967 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**  
No **Switchable:**

### Physical & Mechanical Properties

40.00 **Length (mm):**  
**Width (mm):**

40.00

**Thickness (mm):**

25.40

**Construction:**

Anodized Aluminum

**Weight (kg):**

0.08

**Repeatability (µrad):**

<70.0

## Threading & Mounting

**Mounting Threads:**

(4) 2-56, (4) 6-32, (2) 8-32, (1) 1/4-20

## Material Properties

**Magnetic Force (N):**

10

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 247:**

[Compliant](#)

**Country of Origin:**

Taiwan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.