

[See all 298 Products in Family](#)

TECHSPEC<sup>®</sup> 420nm CWL, 25mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock **#65-136** **20+ In Stock**

[Additional Bandwidths](#)

-

1

+

₹20,007

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹20,007 each                  |
| Qty 6-25       | ₹15,726 each                  |
| Qty 26-49      | ₹14,636 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Bandpass Filter

Type:

**Typical Applications:**  
Glacial Blue, Plum Purple, 7-Diethylaminocoumarin-3-Carboxylic Acid Hydrazide

Physical & Mechanical Properties

|                                                                                                                                                                           |                           |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
| 25.00 +0.0/-0.1                                                                                                                                                           | Diameter (mm):            |
| 21.0                                                                                                                                                                      | Clear Aperture CA (mm):   |
| ±0.1                                                                                                                                                                      | Thickness Tolerance (mm): |
| Mounted in Black Anodized Ring                                                                                                                                            | Construction:             |
| Physical Durability:<br>Adhesion per ML-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per ML-PRF-13830B, Section C.4.5.11<br>Cleaning per ML-C-48497A Section 4.5.4.2 |                           |
| 3.5 ±0.5 typical                                                                                                                                                          | Substrate Thickness (mm): |

|                    |                                          |
|--------------------|------------------------------------------|
| Optical Properties |                                          |
| 0                  | Angle of Incidence (°):                  |
| ≥4.0               | Optical Density OD (Average):            |
| 420.00 ±2.0        | Center Wavelength CWL (nm):              |
| 10.00 ±2.0         | Full Width-Half Max FWHM (nm):           |
| ±2.0               | Full Width-Half Max FWHM Tolerance (nm): |
| Optical Glass      | Substrate: <input type="checkbox"/>      |
| ≥85                | Minimum Transmission (%):                |
| Hard Coated        | Coating:                                 |
| 80-50              | Surface Quality:                         |
| 200 - 1200         | Blocking Wavelength Range (nm):          |

|                      |                       |
|----------------------|-----------------------|
| Threading & Mounting |                       |
| 5.0 ±0.1             | Mount Thickness (mm): |

|                                                                                                                              |  |
|------------------------------------------------------------------------------------------------------------------------------|--|
| Environmental & Durability Factors                                                                                           |  |
| Environmental Durability:<br>Humidity per ML-STD-810H, Section 507.6<br>Temperature per ML-STD-810H, Section 501.7 and 502.7 |  |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Ideal for Life Sciences or Chemical Analysis
  - Available in UV, VIS, and IR Center Wavelengths
  - Feature High Performance Hard Coatings
  - Hard Coated OD 4.0 [5nm](#), [25nm](#), and [50nm](#) Bandpass Filters Also Available
- TECHSPEC® Hard Coated OD 4.0 10nm Bandpass Filters are narrowband filters used extensively in applications including flame photometry, elemental or laser line separation, fluorescence, laser diode cleanup, or chemical detection or analysis. These optical filters offer steep slopes with deep blocking to achieve high performance in demanding applications. TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters feature durable hard coatings to minimize filter degradation while increasing transmission. The bandpass filters are available in UV, VIS, and IR center wavelengths.
- Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts