

TECHSPEC[®] 40mm Dia. x 80mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock #33-422-INK 17 TO 22 D=DAYS

[Other Coating Options](#)



1



₹6,960.00

ADD TO CART

Qty 1-9

₹6,960.00

Qty 10+

₹6,264.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
40.00 ±0.025

Back Focal Length BFL (mm):
77.32

Effective Focal Length EFL (mm): 80.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 8.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 3.00
Radius R₁=R₂ (mm): 81.3
Clear Aperture CA (mm): 39.00
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View