

TECHSPEC® 40mm Diameter, T-Mount Thick Optic Mount



Stock #57-978 **3 In Stock**

- 1 + MRP ₹7,264

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹7,264 each
Qty 5-9	₹6,468 each
Qty 10-25	₹5,983 each
Need More?	Request Quote

Product Downloads

General

Fixed **Type:**

Circular **Type of Optics:**

Function:

Physical & Mechanical Properties

25.0 **Extension Length (mm):**

Black Anodized Aluminum (6061 T6) **Construction:**

28.45 **Total Length (mm):**

48.0 **Outer Diameter (mm):**

38.0 **Clear Aperture CA (mm):**

20.95 **Max. Thickness of Compatible Optics (mm):**

5.0 **Min. Thickness of Compatible Optics (mm):**

Threading & Mounting

40.0 **Diameter of Compatible Optics (mm):**

T-Mount **Thread Type:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **REACH 241:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information

