

[See all 11 Products in Family](#)

TECHSPEC® 40mm, Side Drive, Standard Top, Piezo Tunable Metric Micrometer Stage



Stock #23-582 **2 In Stock**

⊖ 1 ⊕ MRP ₹1,05,935

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,05,935 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Metric **Type:**

Physical & Mechanical Properties

Linear (X) **Type of Movement:**

Crossed Roller Bearing **Guide System:**

Side Drive	Drive Orientation:
40 x 40	Stage Size (mm):
13	Travel (mm):
M6 x 1	Center Hole:
Aluminium Stage	Construction:
0.5	Leadscrew Pitch (mm):
4	Load Capacity (kg):
1.57 x 1.57	Stage Size (inches):
2	Straight Line Accuracy (µm):
30	Pitch (arcsec):
25	Yaw (arcsec):
0.03	Piezo Travel (mm):
20.00	Piezo Resolution (nm):

Optical Properties

Resolution (µm):
10

Hardware & Interface Connectivity

Type of Drive:
Metric Micrometer Coarse Adjustment Piezo Actuator
Fine Adjustment

Threading & Mounting

Mounting Threads:
(1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

Country of Origin:
Japan

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Micrometer with Separate Piezo Actuator for Fine Adjustment
- 40 x 40mm and 70x70mm in English and Metric Hole Patterns Available
- Easily Assembled into X-Y and X-Y-Z Configurations

TECHSPEC® Crossed-Roller Bearing Piezo Tunable Linear Stages feature our [Standard-Top Crossed-Roller Bearing Linear Translation Stages](#) with an integrated piezo actuator for fine positioning with a 20nm resolution. The crossed roller bearing guide system provides a high level of accuracy, rigidity, and load capacity while the piezo movement ensures precision positioning. The piezo controller is easy to connect and use, featuring an indexed voltage control knob to control the actuator movement, and a switchable lock to fix the actuator in place. TECHSPEC® Crossed-Roller Bearing Piezo Tunable Linear Stages are ideal for a range of nan positioning applications such as semiconductor inspection, DNA sequencing, and medical diagnostics. These stages are available with an English 1/4-20 TPI hole pattern or a Metric hole pattern with an M6 center mounting hole, allowing for integration with other [TECHSPEC® Manual Translation Stages](#) to create any number of axes in different configurations.

[TECHSPEC Z-Axis Brackets](#) are available to use with our translation stages to configure your own X-Y-Z multi-axis positioning system. TECHSPEC Bottom Adapter Plates provide an easy and convenient way of mounting the 40mm stages to standard breadboards. No adapter plate is required for the 70mm translation stages which can be mounted directly onto breadboards. A controller and power supply are required for use with the piezo actuator.