

[See all 5 Products in Family](#)

## 40mm Sq x 125mm FL 30° Off-Axis Parabolic Mirror



High Performance Off-Axis Parabolic Mirrors

Stock **#90-976** [CONTACT US](#)

MRP ₹1,39,733

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹1,39,733 each
Qty 10-25	₹1,25,810 each
Qty 26-49	₹1,19,050 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Off-Axis Parabolic Mirror **Type:**

### Physical & Mechanical Properties

40.0 x 40.0 **Dimensions (mm):**

**Center Thickness CT (mm):**

16.00	<b>Center Thickness Tolerance (mm):</b>
±0.2	
90.00	<b>Clear Aperture (%):</b>
+0.0/-0.2	<b>Dimensional Tolerance (mm):</b>
40.00	<b>Length (mm):</b>
40.00	<b>Width (mm):</b>
<b>Optical Properties</b>	
±2.0	<b>Y Offset Tolerance (mm):</b>
Metal	<b>Coating Type:</b>
Bare Aluminum	<b>Coating:</b>
30	<b>Off-Set Angle (°):</b>
134.00	<b>Effective Focal Length EFL (mm):</b>
Float Glass	<b>Substrate:</b> <input type="checkbox"/>
R <sub>abs</sub> >85% @ 250 - 700nm	<b>Coating Specification:</b>
125.0	<b>Parent Focal Length PFL (mm):</b>
±0.5%	<b>Parent Focal Length Tolerance (mm):</b>
λ/2	<b>Surface Accuracy:</b>
80-50	<b>Surface Quality:</b>
268.00	<b>Radius of Curvature (mm):</b>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Japan	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- High Quality Glass Substrate
- λ/4 or λ/2 Surface Accuracy
- Ideal for UV and Visible Applications

Our High Performance Off-Axis Parabolic Mirrors feature a superior surface accuracy glass substrate, making them ideal for UV and visible applications. Unlike standard parabolic mirrors, these off-axis mirrors direct and focus incident collimated light at a specific angle, allowing unrestricted access to the focal point. Typical applications include use in Czerny-Turner and Littrow spectrometer configurations, and in general collimator and beam expander setups.

High Performance Off-Axis Parabolic Mirrors have been replicated from masters which have passed stringent inspection criteria, including zonal interferometric and Foucault testing. The aspheric optical profile is holographically recorded onto the mirror substrate.

**Note:** The bare aluminum coating on these optics is delicate and can be easily scratched. If cleaning is required, non-contact methods such as compressed air or an air-blower should be used.

## Technical Information

Parent Focal Length PFL	Reflected Effective Focal Length EFL	Y Offset	V	Off-Set Angle	Stock No.
125mm	134mm	67mm	9mm	30°	<a href="#">#90-976</a>
200mm	209mm	85mm		24°	<a href="#">#90-977</a>
275mm	279.1mm	67.5mm	4.1mm	14°	<a href="#">#90-978</a> <a href="#">#90-980</a>


277.6mm

53mm

2.6mm

11°

#90-979



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools