

**TECHSPEC® 45° AOI, 101 x 127mm, Cold Mirror**



TECHSPEC High Performance Cold Mirrors

Stock **#64-452** **20+ In Stock**

MRP ₹24,012

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹24,012 each
Qty 10-25	₹21,590 each
Qty 26-49	₹20,481 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cold Mirror **Type:**

**Physical & Mechanical Properties**

3.30 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

101.0 x 127.0

**Dimensional Tolerance (mm):**

+0.0/-0.2

**Length (mm):**

127.00

**Width (mm):**

101.00

## Optical Properties

**Transmission (%):**

Dichroic Filter

**Coating Type:**

Dielectric

**Coating:**

Cold Mirror, 45°

**Surface Flatness (P-V):**

4 - 6λ

**Wavelength Range (nm):**

425 - 1150

**Substrate:**

**BOROFLOAT®**

**Angle of Incidence (°):**

45

**Coating Specification:**

R<sub>avg</sub> ≥ 95% @ 400 - 690nm and T<sub>avg</sub> ≥ 90% @ 750 - 1200nm

AR Coating: R<sub>avg</sub> < 1% @ 700 - 1150nm

**Surface Quality:**

80-50

## Regulatory Compliance

**RoHS 2015:**

**Compliant**

**Certificate of Conformance:**

[View](#)

**Reach 247:**

**Compliant**

**Country of Origin:**

United States

**Imported By:**



Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

## Technical Information



**Quote Your Size**

**Compatible Mounts**

---