

TECHSPEC<sup>®</sup> 473nm CWL, 12.5mm Dia., Hard Coated OD 4.0 10nm Bandpass Filter



TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters

Stock **#34-502** **7 In Stock**

-

1

+

₹13,390

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹13,390 each                  |
| Qty 6-25       | ₹10,510 each                  |
| Qty 26-49      | ₹9,887 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                            |                       |
|----------------------------------------------------|-----------------------|
| Bandpass Filter                                    | Type:                 |
| 473nm Coherent <sup>®</sup> OBIS <sup>™</sup> Line | Typical Applications: |
| Physical & Mechanical Properties                   |                       |
| 12.50 +0.0/-0.1                                    | Diameter (mm):        |

|                                                                                                                                                                                     |                           |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
| 8.5                                                                                                                                                                                 | Clear Aperture CA (mm):   |
| ±0.1                                                                                                                                                                                | Thickness Tolerance (mm): |
| Mounted in Black Anodized Ring                                                                                                                                                      | Construction:             |
| <b>Physical Durability:</b><br>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497A Section 4.5.4.2 |                           |
| 3.5 ±0.5 typical                                                                                                                                                                    | Substrate Thickness (mm): |

| Optical Properties |                                          |
|--------------------|------------------------------------------|
| 0                  | Angle of Incidence (°):                  |
| ≥4.0               | Optical Density OD (Average):            |
| 473.00 ±2.0        | Center Wavelength CWL (nm):              |
| 10.00 ±2.0         | Full Width-Half Max FWHM (nm):           |
| ±2.0               | Full Width-Half Max FWHM Tolerance (nm): |
| Optical Glass      | Substrate: □                             |
| ≥85                | Minimum Transmission (%):                |
| Hard Coated        | Coating:                                 |
| 80-50              | Surface Quality:                         |
| 200 - 1200         | Blocking Wavelength Range (nm):          |

| Threading & Mounting |                       |
|----------------------|-----------------------|
| 5.0 ±0.1             | Mount Thickness (mm): |

| Environmental & Durability Factors                                                                                                    |  |
|---------------------------------------------------------------------------------------------------------------------------------------|--|
| <b>Environmental Durability:</b><br>Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7 |  |

| Regulatory Compliance               |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |




## Product Details

- Ideal for Life Sciences or Chemical Analysis
- Available in UV, VIS, and IR Center Wavelengths
- Feature High Performance Hard Coatings
- Hard Coated OD 4.0 **5nm**, **25nm**, and **50nm** Bandpass Filters Also Available




TECHSPEC® Hard Coated OD 4.0 10nm Bandpass Filters are narrowband filters used extensively in applications including flame photometry, elemental or laser line separation, fluorescence, laser diode cleanup, or chemical detection or analysis. These optical filters offer steep slopes with deep blocking to achieve high performance in demanding applications. TECHSPEC Hard Coated OD 4.0 10nm Bandpass Filters feature durable hard coatings to minimize filter degradation while increasing transmission. The bandpass filters are available in UV, VIS, and IR center wavelengths.

**Note:** These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). Atypical LIDT for these filters is 1 J/cm<sup>2</sup> @ 532nm, 10ns. Please [contact us](#) if you require a filter with a higher LIDT value.

## Technical Information



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we

provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

---