

488nm High Performance Laser Line Filter 25mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#64-250** **1 In Stock**

☐ [Additional Bandwidths](#)

-

1

+

₹61,346

ADD TO CART

Volume Pricing	
Qty 1+	₹61,346 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
25.00 +0.0/-0.1	Diameter (mm):
≥22	Clear Aperture CA (mm):
±0.10	Thickness Tolerance (mm):

Mounted in Black Anodized Ring	Construction:
ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	Physical Durability:
2.0 ±0.1	Substrate Thickness (mm):
Optical Properties	
0 ±2	Angle of Incidence (°):
1.9	Bandwidth (nm):
<11	Beam Deviation (arcsec):
415 - 483 & 493 - 625	OD 5 Blocking Wavelength Range (nm) :
449 - 481 & 495 - 537	OD 6 Blocking Wavelength Range (nm):
≥6.0	Optical Density OD (Average):
488.00	Center Wavelength CWL (nm):
488	Design Wavelength DWL (nm):
1.85 - 3.42	Full Width-Half Max FWHM (nm):
Fused Silica	Substrate: □
>90	Minimum Transmission (%):
Hard Coated	Coating:
60-40	Surface Quality:
>90	Transmission (%):
415 - 483 & 493 - 625	Blocking Wavelength Range (nm):
¼ @ 633nm	Transmitted Wavefront, P-V:
Threading & Mounting	
3.5 ±0.1	Mount Thickness (mm):
Environmental & Durability Factors	
<5	Temperature Dependence (ppm/°C):
ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	Environmental Durability:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:







Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts