

[See all 10 Products in Family](#)

**TECHSPEC® 45mm EFL MgF<sub>2</sub> Coated, UV-NIR Corrected Triplet**



Stock #64-837 [CONTACT US](#)

- 1 + MRP ₹2,88,545

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹2,88,545 each
Qty 6-10	₹2,45,163 each
Qty 11-25	₹2,31,038 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Achromatic Triplet Lens **Type:**

**Physical & Mechanical Properties**

22.5 **Clear Aperture CA (mm):**

30.00 ±0.05 **Housing Diameter (mm):**

Housing Length (mm):  
27.50 ±0.05

## Optical Properties

Effective Focal Length EFL (mm):  
45.00

Focal Length Tolerance (%):  
±1.5 @248nm

Back Focal Length BFL (mm):  
34.84

Back Focal Length BFL from Housing (mm):  
33.3

Substrate:   
CaF<sub>2</sub> / Fused Silica / CaF<sub>2</sub>

Surface Quality:  
60-40

f#:  
2.00

Numerical Aperture NA:  
0.25

Coating:  
MgF<sub>2</sub> (193-1000nm)

Coating Specification:  
MgF<sub>2</sub> @600nm

Effective Focal Length EFL @ 248nm (mm):  
45.00

Wavelength Range (nm):  
193 - 1000

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Reach 224:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Country of Origin:  
United States

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Calcium Fluoride and UV Fused Silica Elements
- Broadband Color-Corrected Design from 193nm to 1000nm
- Ideal for Fluorescence and Spectroscopy Applications

TECHSPEC® UV-to-NIR Corrected Triplet Lenses provide a consistent focal length (see chromatic shift information below) for wavelengths ranging from 193nm to 1000nm. These lenses were designed with broadband applications in mind. Manufactured with premier grades of Calcium Fluoride and Fused Silica, these infinite-conjugate triplets are perfect for imaging applications utilizing a wide spectrum of wavelengths. TECHSPEC® UV-to-NIR Corrected Triplet Lenses are typically used for fluorescence research in which the emitted light is in the visible and near infrared regions of the spectrum or in dual-pass systems in which the same lens is used to illuminate the excitation material as well as collect the emissions from it. Elements are uncoated and mounted in a 30mm diameter aluminum housing. Antireflection coatings available, however a minimum order quantity will apply.

Full [prescription](#) information available.

## Technical Information



Effective Focal Length EFL	193 - 400nm		400 - 1000nm		193 - 1000nm	
	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size
36mm	1.8mm	240µm	0.4mm	214µm	2.2mm	268µm
45mm	1.1mm	88µm	0.3mm	69µm	1.3mm	95µm
90mm	2.0mm	64µm	0.6mm	38µm	2.5mm	69µm
135mm	1.6mm	49µm	0.6mm	31µm	2.1mm	51µm
180mm	1.4mm	46µm	0.6mm	28µm	1.9mm	45µm