

TECHSPEC® 4mm, Alum. & AR Coated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock **#47-924** [CONTACT US](#)

- 1 + **₹10,092.00**

ADD TO CART

Qty 1-5
₹10,092.00
Qty 6+
₹9,083.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate: ☐
[N-SF11](#)

Surface Quality:
20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.05
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 5.70
Length of Legs (mm): 4.00
Image Orientation: Left-Handed
Coating Specification: Legs: R _{avg} ≤1.75% @ 400 - 700nm Hypotenuse: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/4
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @532nm & 1064nm, 10ns Legs: 10 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View