

[See all 12 Products in Family](#)

4mm Diameter, Truncated B270 Half-Ball Lens



B270 Half-Ball Lenses

Stock #21-900 **11 In Stock**

1 MRP ₹3,734

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-10	₹3,734 each
Qty 11-25	₹3,153 each
Qty 26-49	₹2,825 each
Need More?	Request Quote

Product Downloads

General

Half-Ball Lens **Type:**

Physical & Mechanical Properties

4.00 ±0.1 **Diameter (mm):**

Center Thickness CT (mm):

1.70 ±0.15

2.00 **Radius R (mm):**

Optical Properties

B270 **Substrate:** □

Uncoated **Coating:**

360 - 2700 **Wavelength Range (nm):**

1.523 **Index of Refraction (n_d):**

Regulatory Compliance

Compliant **RoHS 2015:**

Compliant **Reach 224:**

View **Certificate of Conformance:**

Germany **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

B270 Half-Ball Lenses feature a molded spherical surface and polished plano surface, facilitating easier mounting compared to ball lenses. The B270 substrates have high transmission from the visible to the near infrared (NIR) and have a similar refractive index to N-BK7, making these lenses an ideal alternative for cost sensitive applications. Each diameter of lens is available in two form factors, truncated (hypo-hemisphere) and extended (hyper-hemisphere), providing options to best meet system mechanical requirements. B270 Half-Ball Lenses are used in high power LED, fiber coupling, endoscopy, microscopy, and laser measurement applications.