

[See all 156 Products in Family](#)

TECHSPEC[®] 4" Dia. Enhanced Aluminum, λ /20 Flat Fused Silica



Stock **#47-574-533** **2 In Stock**

-

1

+

₹80,964

ADD TO CART

Volume Pricing	
Qty 1-5	₹80,964 each
Qty 6-10	₹72,790 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror

Type:

Flatness is specified as Peak to Valley

Note:

Physical & Mechanical Properties

101.60 +0.0/-1.02

Diameter (mm):

19.10 ±1.5	Thickness (mm):
Commercial Polish	Back Surface:
91.44	Clear Aperture CA (mm):

+0.0/-0.04	Diameter Tolerance (inches):
------------	------------------------------

Optical Properties

0.45 - 0.65	Wavelength Range (µm):
Metal	Coating Type:

Enhanced Aluminum (450-650nm)	Coating:
λ/20	Surface Flatness (P-V):

450 - 650	Wavelength Range (nm):
Fused Silica (Corning 7980)	Substrate: □

R _{avg} >95% @ 450 - 650nm	Coating Specification:
60-40	Surface Quality:

0.2 J/cm ² @ 532nm, 10ns	Damage Threshold, Reference: □
-------------------------------------	--------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 247:
-----------	------------

United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Fused Silica and ZERODUR® Substrates
- λ/10 and λ/20 Surface Flatness
- Variety of Coating Options Offered

TECHSPEC® Precision Optical Flat Mirrors are ideal for various applications, including interferometry, imaging systems, laser applications, optical path folding, and autocollimation. These mirrors are available in multiple coating and substrate options and surface flatness options of λ/10 and λ/20. The first substrate option ZERODUR®, a yellow-tinted glass ceramic, features an extremely low coefficient of thermal expansion. TECHSPEC® Precision Optical Flat Mirrors are ideal for applications where temperature fluctuation is a concern using the ZERODUR® substrate. The second option, Fused Silica, is optically clear and features excellent resistance to abrasion and high durability, making it the best choice for applications in harsh environments. Please note, calibration certificates are not supplied with these parts.

[TECHSPEC® λ/10 and λ/20 Precision Optical Flats](#) are available for testing and measurement applications.

Note: Surface flatness specifications are measured before coating.

Coating Curves

Compatible Mounts

