

4mm 2 MegaPixel Fixed Focal Length Lens



4mm Fixed Focal Length, #14-394

Stock **#14-394** **1 In Stock**

MRP ₹72,747

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹72,747 each
Need More?	Request Quote

Product Downloads

General

Fixed Focal Length Lens **Type:**

Physical & Mechanical Properties

Variable **Iris Option:**

35.97 **Length (mm):**

44.5 **Maximum Diameter (mm):**

Weight (g):

130

Optical Properties

Horizontal Field of View @ Max Sensor Format:
77.4°

Horizontal Field of View, 1/2" Sensor:
77.4°

Horizontal Field of View, 1/3" Sensor:
61.93°

Horizontal Field of View, 1/4" Sensor:
43.6°

Maximum Image Circle (mm):
8.00

Focal Length FL (mm):
4.00

Working Distance (mm):
100 - ∞

Aperture (f/#):
f/2 - f/16

Distortion (%):
<-2.8

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/2"

Threading & Mounting

Mount:
C-Mount

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover 1/2" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.