

[See all 19 Products in Family](#)

## 4mm Aperture VIS/NIR Fiber Optic Collimator, FC



4mm Aperture Fiber Optic Collimator, FC

Stock **#88-188** **6 In Stock**

1  MRP ₹20,783

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-10	₹20,783 each
Qty 11-24	₹18,463 each
Qty 25-49	₹17,353 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Fiber Collimator

Type:

0.22

Compatible Fiber NA:

Stainless Steel

Housing Material:

Note:

## Physical & Mechanical Properties

6.35 **Diameter (mm):**

4.0 **Aperture Size:**

19.70 **Length (mm):**

## Optical Properties

**N-BK7** **Substrate:**

350 - 2200 **Wavelength Range (nm):**

compatible up to 400 **Fiber Diameter (µm):**

10.00 **Focal Length FL (mm):**

## Hardware & Interface Connectivity

FC **Connector:**

## Environmental & Durability Factors

-40 to 100 **Operating Temperature (°C):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 209:**

**View** **Certificate of Conformance:**


United States **Country of Origin:**

**Imported By:**  
 Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000


## Product Details

- Can Be Coupled to Standard 0.22 NA Fiber Optic Cables
- Options Available for UV-VIS or VIS-NIR
- Multiple Focal Length or Aperture Options

Focusable Collimators consist of two separate components: a fiber optic collimator and a fiber optic refocusing assembly. The fiber optic collimator utilizes a PCX lens positioned at the focal length from the optical fiber tip. These collimators are available with FC or SMA threads, and easily couple to standard 0.22 NA fiber optic cables. Focusable Collimators expand the beam and decrease the divergence by the ratio of the fiber core diameter to the collimator aperture. Fiber optic refocusing assemblies mount directly to the fiber optic collimator and allow for optimal focus at a given distance.




## Technical Information




The 4mm Aperture Fiber Optic Collimator threads directly onto FC or SMA fiber.

**Fiber with 10mm Aperture Fiber Optic Collimator**



Each 10mm Aperture Fiber Optic Collimator includes an FC or SMA adapter that is inserted into the collimator and locked by a set screw.

**Fiber with 10mm Aperture Fiber Optic Collimator and Refocusing Assembly**



A 10mm Aperture Refocusing Assembly can then be directly threaded onto the 10mm Aperture Fiber Optic Collimator.

Collimator Description	Stock Number	Compatible Refocusing Assembly
4mm Aperture UV/MS Fiber Optic Collimator, FC	<a href="#">#88-189</a>	No Compatible Refocusing Assemblies
4mm Aperture UV/MS Fiber Optic Collimator, SMA	<a href="#">#88-173</a>	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, FC	<a href="#">#88-188</a>	No Compatible Refocusing Assemblies
4mm Aperture VIS/NIR Fiber Optic Collimator, SMA	<a href="#">#88-172</a>	No Compatible Refocusing Assemblies
10mm Aperture UV/MS Fiber Optic Collimator, FC	<a href="#">#88-191</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture UV/MS Fiber Optic Collimator, SMA	<a href="#">#88-181</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture VIS/NIR Fiber Optic Collimator, FC	<a href="#">#88-190</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>
10mm Aperture VIS/NIR Fiber Optic Collimator, SMA	<a href="#">#88-180</a>	<a href="#">#88-182</a> , <a href="#">#88-183</a> , <a href="#">#88-184</a> , <a href="#">#88-185</a> , <a href="#">#88-186</a> , & <a href="#">#88-187</a>