

TECHSPEC[®] 50 x 50mm, 400 - 750nm Broadband $\lambda/10$ Mirror



Stock **#29-921** [CONTACT US](#)

-

1

+

₹19,751

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹19,751 each
Qty 6-25	₹15,800 each
Qty 26-49	₹14,836 each
Need More?	Request Quote

Product Downloads

General

Type:
Flat Mirror

Physical & Mechanical Properties

Thickness (mm):
5.00 ±0.20

50.00 x 50.00 +0.00/-0.20	Dimensions (mm):
Commercial Polish	Back Surface:
90	Clear Aperture (%):
Ground, 0.5mm max bevel	Edges:
<0.5	Parallelism (arcmin):
30	Parallelism (arcsec):

Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (400-750nm)	Coating:
$\lambda/10$	Surface Flatness (P-V):
400 - 750	Wavelength Range (nm):
Fused Silica (Corning 7980)	Substrate: ☐
0-45	Angle of Incidence (°):
R _{avg} >98% @400 - 750nm (0 - 45°) R _{avg} >99% @400 - 750nm (0°)	Coating Specification:
20-10	Surface Quality:
0.5 J/cm ² @ 532nm, 20ns, 20Hz	Damage Threshold, Reference: ☐

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Enhanced Reflectivity and LIDT over Metallic Coatings
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Designed for all Polarization States from 0 – 45° AOI

TECHSPEC® Broadband Dielectric $\lambda/10$ Mirrors are ideal for beam steering or reflection applications utilizing multiple laser sources. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. The highly durable fused silica substrate offers a low thermal expansion coefficient and a high abrasion resistance. TECHSPEC® Broadband Dielectric $\lambda/10$ Mirrors are designed for applications from the UV to the near-infrared spectra.

Technical Information

