

TECHSPEC<sup>®</sup> 50 x 50mm High-Temperature Linear Polarizing Film (XP40HT-18)



High-Temperature Linear Polarizing Film (XP40HT)

Stock **#13-912** CLEARANCE **20+ In Stock**

-

1

+

₹2,246

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹2,246 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Linear Polarizer

Type:

Note:

Polarization axis can be identified as follows:  
Circular Parts - Parallel to direction of notch on polarizer  
Square Parts - Parallel to mark on protective film

Rectangular Parts - Parallel to first listed dimension

### Physical & Mechanical Properties

50.0 x 50.0 +0.0/-0.5

Dimensions (mm):

0.19 ±0.02

Thickness (mm):

Polarizing Film

Construction:

### Optical Properties

Uncoated, Protective Film on Both Sides

Coating:

5000:1

Extinction Ratio:

Polymer Film XP40HT-18

Substrate: □

400 - 700

Wavelength Range (nm):

>99.5

Polarization Efficiency (%):

40 ±2

Transmission, Single (%):

32.2

Transmission, Parallel (%):

<0.005

Transmission, Crossed (%):

<±10

Transmission Variance after 1000 Hours (%):

### Environmental & Durability Factors

100 x 1,000

Heat Resistance (°C x Hours):

-40 x 1,000

Cold Resistance (°C x Hours):

80 x 90% RH x 1,000

Humidity Resistance (°C x Hours):

### Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Contains SVHC(s)

Reach 235:

## PRODUCT DETAILS

- High-Temperature Resistance Compared with Common Polarizing Films
- Extinction Ratio of 5000:1
- High Transmission of Unpolarized Light from 400 - 700nm
- Custom Sizes Available

TECHSPEC® High-Temperature Linear Polarizing Film (XP40HT) provides a significantly better temperature resistance of 100°C over 1000 hours compared to [common linear polarizing films](#). These polarizers feature a high extinction ratio, excellent polarization efficiency, and exceptional transmission in the visible spectrum from 400 to 700nm. A variety of standard sizes from 10mm dia. to 600 x 1000mm are available with custom sizes available on request. TECHSPEC High-Temperature Linear Polarizing Film (XP40HT) is especially well suited for applications where higher temperatures are unavoidable including photography using illumination systems or in harsh environments, 3D projection systems, and optical inspection systems.

**Note:** Remove protective liner from both surfaces before first use. Polarizer Film with adhesive available.

### Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High-Temperature Linear Polarizing Film (XP40HT) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.