

[See all 13 Products in Family](#)

4X, 532nm Jenoptik Fixed Beam Expander

See More by [Jenoptik](#)



Stock #73-115 [CONTACT US](#)

MRP ₹77,905

Price inclusive of all taxes

[ADD TO CART](#)

Volume Pricing	
Qty 1-4	₹77,905 each
Qty 5+	₹70,257 each
Need More?	Request Quote

Product Downloads

General

Beam Expander **Type:**

Diffraction Limited up to an 1/e² Diameter of 5mm **Note:**

Fixed Magnification **Style:**

Physical & Mechanical Properties

Length (mm):

132.60

Weight (g):

297

Optical Properties

Entrance Aperture (mm):

12

Exit Aperture (mm):

40

Expansion Power:

4X

Transmission (%):

99

Design Wavelength DWL (nm):

532

Wavelength Range (nm):

515 - 540

Damage Threshold, Reference:

CW: 2.5 MW/cm² Pulsed (ns): 2.5 J/cm²

GDD Specification (fs²):

659

Threading & Mounting

Mounting Threads:

Input: M30 x 1
Output: M50 x 1

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for High-Power and Ultrashort Pulse Systems
- Fixed Magnifications Available from 1.5X to 8X
- Designed for Diffraction Limited Performance

Jenoptik Fixed Magnification Beam Expanders provide diffraction limited performance with high damage thresholds for the demanding requirements of laser materials processing. These beam expanders are coated to maximize transmission at Nd:YAG laser wavelengths of 266, 355, 532, and 1064nm are available in multiple fixed magnifications from 1.5X to 8X. A stainless-steel housing and optical elements made from robust quartz glass ensure maximum resistance and durability. Jenoptik Fixed Magnification Beam Expanders are ideal for a range of high-power laser material processing applications including cutting, welding, and engraving for metals, polymers, or ceramics. M50 x 1.0 threading on the front and M30 x 1.0 threading on the rear of the housing allow for ease of system integration as well as ease of setup for reverse operation.