

TECHSPEC<sup>®</sup> 14.0" Dia. Enhanced Aluminum,  $\lambda/20$  Flat ZERODUR<sup>®</sup>



Stock #71-247-533

CONTACT US

-

1

+

₹10,41,570

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹10,41,570 each               |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

SPECIFICATIONS

General

Flatness is specified as Peak to Valley

Note:

Flat Mirror

Type:

| Physical & Mechanical Properties    |                                          |
|-------------------------------------|------------------------------------------|
| 355.60 +0.0/-1.0                    | Diameter (mm):                           |
| Commercial Polish                   | Back Surface:                            |
| 14.00 +0.0/-0.04                    | Diameter (inches):                       |
| 320.04                              | Clear Aperture CA (mm):                  |
| 88.90 ±2.0                          | Thickness (mm):                          |
| Optical Properties                  |                                          |
| λ/10                                | Surface Flatness (P-V):                  |
| ZERODUR®                            | Substrate: <div></div>                   |
| 60-40                               | Surface Quality:                         |
| R <sub>avg</sub> >95% @ 450 - 650nm | Coating Specification:                   |
| Enhanced Aluminum (450-650nm)       | Coating:                                 |
| Metal                               | Coating Type:                            |
| 0.45 - 0.65                         | Wavelength Range (μm):                   |
| 450 - 650                           | Wavelength Range (nm):                   |
| 0.2 J/cm² @ 532nm, 10ns             | Damage Threshold, Reference: <div></div> |
| Regulatory Compliance               |                                          |
| <a href="#">View</a>                | Certificate of Conformance:              |

## PRODUCT DETAILS

- Fused Silica and ZERODUR® Substrates
- λ/10 and λ/20 Surface Flatness
- Variety of Coating Options Offered

TECHSPEC® Precision Optical Flat Mirrors are ideal for various applications, including interferometry, imaging systems, laser applications, optical path folding, and autocollimation. These mirrors are available in multiple coating and substrate options and surface flatness options of λ/10 and λ/20. The first substrate option ZERODUR®, a yellow-tinted glass ceramic, features an extremely low coefficient of thermal expansion. TECHSPEC® Precision Optical Flat Mirrors are ideal for applications where temperature fluctuation is a concern using the ZERODUR® substrate. The second option, Fused Silica, is optically clear and features excellent resistance to abrasion and high durability, making it the best choice for applications in harsh environments. Please note, calibration certificates are not supplied with these parts.

**TECHSPEC® λ/10 and λ/20 Precision Optical Flats** are available for testing and measurement applications.

**Note:** Surface flatness specifications are measured before coating.

## COATING CURVES

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).