


TECHSPEC®

50 x 50mm Linear Polarizing Film (XP42-40)



Stock #19-007 CLEARANCE 10 TO 12 DAYS

-

1

+

₹2,088.00

ADD TO CART

Qty 1-10
₹2,088.00
Qty 11+
₹1,827.00
Volume Pricing
Request Quote

Get Product Downloads

Extinction Ratio:
9000:1 (nominal at 555nm)

Substrate: [Polymer Film XP42-40](#)

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
50.0 x 50.0

Thickness (mm): 0.40 ±0.05
Transmission (%): Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): ±1.0
Construction: Polarizing Film
Note: Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98 (nominal at 555nm)
Transmission Variance after 1000 Hours (%): <±5
#Sorting: 43.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)