


50 x 50mm NIR Linear Polarizing Film



Stock #12-474 10 TO 12 DAYS

- 1 + ₹33,930.00

ADD TO CART

Qty 1-10
₹33,930.00

Qty 11+
₹32,364.00

Volume Pricing
Request Quote

Get Product Downloads

Coating: Uncoated
Extinction Ratio: 400:1 (Average @ 800 - 2200nm)
Substrate: ☐ Polymer Film on TAC
Length (mm): 50.00

Operating Temperature (°C): Heat Resistance 85°C Dry Cold Resistance -55°C
Dimensions (mm): 50.0 x 50.0
Thickness (mm): 0.50
Thickness Tolerance (mm): ±0.1
Transmission (%): Single: 29 (400 - 760 nm), 39 (761 - 2200nm) Crossed: 0.02 (400 - 760nm), 0.11 (761 - 2200nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): ±0.25
Construction: Polarizing Film
Note: Protective Film on Both Sides
Wavelength Range (nm): 400 - 2200
Polarization Efficiency (%): 99.83 @ 400 - 760nm 99.63 @ 761 - 2200nm
Width (mm): 50.00
Transmission, Single (%): 29 @ 400 - 760nm 39 @ 761 - 2200nm
Transmission, Crossed (%): 0.02 @ 400 - 760nm 0.11 @ 761 - 2200nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View