

TECHSPEC® 50.8mm Dia. 355nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#38-870** 10 TO 12 DAYS

⊖ 1 ⊕ **₹25,404.00**

ADD TO CART

Qty 1-5
₹25,404.00
Qty 6+
₹22,533.00
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):

90
Back Surface: Commercial Polish
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} ≥99.8% @ 355nm
Wavelength Range (nm): 351 - 358
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (355nm)
Design Wavelength DWL (nm): 355
Diameter (mm): 50.80 +0.00/-0.10
Thickness (mm): 9.53 ±0.2
Angle of Incidence (°): 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, Reference: ☐ 5 J/cm ² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View