

[See all 12 Products in Family](#)

**TECHSPEC® 50.0mm Dia x 5mm Thick 635-670/1064nm, Zerodur Dual Band Laser Mirror**



Stock #29-067 **4 In Stock**

- 1 + MRP ₹39,751

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹39,751 each
Qty 6-25	₹31,781 each
Qty 26-49	₹29,813 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**

**Physical & Mechanical Properties**

5.00 ±0.20 **Thickness (mm):**

50.00 +0.00/-0.20 **Diameter (mm):**

90	<b>Clear Aperture (%):</b>
30	<b>Parallelism (arcsec):</b>
Commercial Polish	<b>Back Surface:</b>
Protective as needed	<b>Bevel:</b>
Ground	<b>Edges:</b>

## Optical Properties

ZERODUR®	<b>Substrate:</b> □
20-10	<b>Surface Quality:</b>
Laser Mirror (635, 670, 1064nm)	<b>Coating:</b>
635, 670, 1064	<b>Design Wavelength DWL (nm):</b>
Rabs >99.5% @ 635, 670 & 1064nm	<b>Coating Specification:</b>
Dielectric	<b>Coating Type:</b>
20 J/cm2 @ 1064nm	<b>Damage Threshold, By Design:</b> □

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- >99.5% Reflectivity at Design Wavelengths
- Low Coefficient of Thermal Expansion
- 532/1064nm or 635/670/1064nm Wavelength Bands

TECHSPEC® Zerodur® Dual Band Laser Line Mirrors feature high reflectivity coatings with either two or three wavelength bands on a durable Zerodur® substrates. The ZERODUR® substrates have a low coefficient of thermal expansion (CTE) of  $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ , which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® Zerodur® Dual Band Laser Line Mirrors are available in a highly reflective 532/1064nm or 635/670/1064nm dual band coatings and multiple standard diameter options for Nd:YAG lasers and red and green guide beams. These mirrors are ideal for beam steering applications in both laboratory and OEM laser systems.