

[See all 102 Products in Family](#)

TECHSPEC<sup>®</sup> 50.0mm Diameter x 150.0mm FL, 1550nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#84-272 4 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹5,372

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹5,372 each                   |
| Qty 10-25      | ₹4,827 each                   |
| Qty 26-49      | ₹4,321 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

|                           |                      |
|---------------------------|----------------------|
| 50.00 +0.0/-0.025         |                      |
| Centering (arcmin):       | <1                   |
| Center Thickness CT (mm): | 9.00 ±0.10           |
| Edge Thickness ET (mm):   | 4.86                 |
| Clear Aperture CA (mm):   | 49                   |
| Bevel:                    | Protective as needed |

|                                  |                                    |
|----------------------------------|------------------------------------|
| Optical Properties               |                                    |
| Effective Focal Length EFL (mm): | 150.00 @587.6nm                    |
| Back Focal Length BFL (mm):      | 144.07                             |
| Coating:                         | Laser V-Coat (1550nm)              |
| Coating Specification:           | R <sub>abs</sub> <0.25% @ 1550nm   |
| Substrate: □                     | N-BK7                              |
| Surface Quality:                 | 40-20                              |
| Power (P-V) @ 632.8nm:           | 1.5λ                               |
| Irregularity (P-V) @ 632.8nm:    | λ/4                                |
| Focal Length Tolerance (%):      | ±1                                 |
| Radius R <sub>1</sub> (mm):      | 77.52                              |
| f/#:                             | 3.00                               |
| Numerical Aperture NA:           | 0.17                               |
| Design Wavelength DWL (nm):      | 1550                               |
| Damage Threshold, By Design: □   | 5 J/cm <sup>2</sup> @ 1550nm, 10ns |

|                             |                                     |
|-----------------------------|-------------------------------------|
| Regulatory Compliance       |                                     |
| RoHS 2015:                  | Compliant                           |
| Certificate of Conformance: | View                                |
| Reach 235:                  | Compliant                           |
| Country of Origin:          | Japan                               |
| Importer:                   | Edmund Optics India Private Limited |

## Product Details

- <0.25% Reflection at Design Wavelength
  - Coatings Available for Diode, HeNe, and Nd:YAG Laser Sources
  - BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
  - [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), [1064nm](#), and 1550nm V-Coated Options Offered
- TECHSPEC® 1550nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 1550nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [785nm](#), [980nm](#), and [1064nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
  - High-precision surface quality and flatness
  - Tight tolerances and complex geometries
  - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

