

[See all 133 Products in Family](#)

TECHSPEC® 50.8 x 108.9mm EFL 30° Protected Gold 100Å Off-Axis Parabolic Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock #35-495 3 In Stock

☐ Other Coating Options

-

1

+

₹42,039

ADD TO CART

Volume Pricing	
Qty 1-5	₹42,039 each
Qty 6-25	₹37,835 each
Qty 26-50	₹33,631 each
Need More?	Request Quote

Product Downloads

General

Type:

Off-Axis Parabolic Mirror

Physical & Mechanical Properties

Y Offset (mm):

54.45

Diameter (mm):


50.80 +0.00/-0.38	
90	Clear Aperture (%):
<100 RMS	Surface Roughness (□):
Optical Properties	
Metal	Coating Type:
Protected Gold (700-10000nm)	Coating:
30	Off-Set Angle (°):
700 - 10000	Wavelength Range (nm):
108.89	Effective Focal Length EFL (mm):
Aluminum 6061-T6	Substrate: □
R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm	Coating Specification:
±1	Focal Length Tolerance (%):
101.6	Parent Focal Length PFL (mm):
λ/2	Surface Figure, RMS:
80-50	Surface Quality:
203.20	Radius of Curvature (mm):
1λ	Reflected Wavefront, RMS:
Threading & Mounting	
#47-112	Compatible Mounting Plates:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Bare or Protected Gold Coating for NIR and IR Applications
- 50Åand 100ÅSurface Roughness Options
- 15°, 30°, 45°, 60°, or 90° Offset Angles
- Aluminum and Silver Coated Mirrors Also Available

TECHSPEC® Gold Off-Axis Parabolic Mirrors (OAPs) are designed for minimal scatter loss in light focusing applications. Available with bare or protected gold coatings, these OAP mirrors offer excellent reflectivity from the near infrared (NIR) to the far infrared (IR). Multiple surface roughness options are available in offset angles from 15 to 90°, providing flexibility for system designs. TECHSPEC® Gold Off-Axis Parabolic Mirrors are commonly used in IR systems such as FLIR and FTIR, as well as IR lasers including quantum cascade lasers (QCLs). Mounting plates with holes perpendicular to the optical axis for post mounting are also available.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).