

## 50.8 x 50.8 x 1mm High Efficiency Window



Stock **#48-925** **20+ In Stock**

- 1 + MRP ₹2,876

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹2,876 each
Qty 6-25	₹2,421 each
Qty 26-99	₹2,119 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**  
Glass **Type of Window:**

#### Physical & Mechanical Properties

45.72 x45.72 **Clear Aperture CA (mm):**

50.80 x 50.80	<b>Dimensions (mm):</b>
1.00 ±0.25	<b>Thickness (mm):</b>
50.80	<b>Length (mm):</b>
50.80	<b>Width (mm):</b>
±0.76	<b>Dimensional Tolerance (mm):</b>
Protective as needed	<b>Bevel:</b>
≥90	<b>Clear Aperture (%):</b>
Seamed	<b>Edges:</b>

## Optical Properties

0	<b>Angle of Incidence (°):</b>
BBAR (425-700nm)	<b>Coating:</b>
Float Glass	<b>Substrate:</b> □
80-50	<b>Surface Quality:</b>
96.9 Average (typical)	<b>Transmission (%):</b>
R <sub>avg</sub> ≤0.5% @ 425 - 700nm	<b>Coating Specification:</b>
425 - 700	<b>Wavelength Range (nm):</b>

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- High Transmission
- Eliminate Back Reflections and Reduce Glare
- Available in a Wide Range of Sizes

High Efficiency Anti-Reflection (HEAR) Coated Windows feature dual broadband anti-reflection coatings, reducing reflectance to ≤0.5%. Anti-reflection (AR) coatings are applied to optical surfaces to increase the system's throughput and reduce hazards caused by reflections that travel backward through the system and create ghost images. The coating virtually eliminates back reflections, offering improved readability when used in industrial or scientific displays. High Efficiency Anti-Reflection (HEAR) Coated Windows have a high transmission, making them especially suitable for various optical applications. These anti-reflective windows are available in circular and square formats, with a diverse range of sizes offered in each.

Can't find what you need? Get a quick [custom quote](#).

## Technical Information



**Quote Your Size**

**Compatible Mounts**