

TECHSPEC® 50.8 x 152.4mm EFL 90° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock #35-512

10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹35,235.00

ADD TO CART

Qty 1-5
₹35,235.00
Qty 6+
₹31,712.00
Volume Pricing
Request Quote

Get Product Downloads



Type:

Off-Axis Parabolic Mirror

Diameter (mm):

50.80 +0.00/-0.38

Effective Focal Length EFL (mm):

152.40

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 152.40
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 76.2
Surface Figure, RMS: λ/2
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-112
Substrate: Aluminum 6061-T6
Y Offset (mm): 152.4
Reflected Wavefront, RMS: 1λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant