

[See all 23 Products in Family](#)

TECHSPEC[®] 50.8 x 152.4mm EFL 90° Protected Silver 100Å Off-Axis Parabolic Mirror



Stock **#36-597** 2 In Stock

[Other Coating Options](#)

-

1

+

₹38,147

ADD TO CART

Volume Pricing	
Qty 1-5	₹38,147 each
Qty 6-25	₹34,332 each
Qty 26-50	₹30,517 each
Need More?	Request Quote

Product Downloads


General	
Off-Axis Parabolic Mirror	Type:
Physical & Mechanical Properties	
50.80 +0.00/-0.38	Diameter (mm):
<100 RMS	Surface Roughness (□):

90	Clear Aperture (%):
152.4	Y Offset (mm):
Optical Properties	
152.40	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
152.40	Radius of Curvature (mm):
Protected Silver (450-12000nm)	Coating:
Metal	Coating Type:
Coating Specification: R _{avg} ≥98% @ 2,000 - 12,000nm, R _{avg} (typical) 96% @ 450 - 2,000nm	
90	Off-Set Angle (°):
76.2	Parent Focal Length PFL (mm):
λ/2	Surface Figure, RMS:
450 - 12000	Wavelength Range (nm):
80-50	Surface Quality:
Aluminum 6061-T6	Substrate:
1λ	Reflected Wavefront, RMS:
Threading & Mounting	
#47-112	Compatible Mounting Plates:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Protected Silver Coating for Visible and IR Application
 - 100Å Surface Roughness
 - 90° Offset Angle
 - Aluminum and Gold Coated Off-Axis Parabolic Mirrors Also Available
- TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are designed to direct and focus incident collimated light at a specific offset angle with minimal scatter loss. Coated with protected silver, these OAP mirrors provide high reflectivity from the visible to the infrared (IR), making them ideal for broadband applications. These Silver OAPs provide unobstructed access to the point of focus, allowing for the creation of more compact systems. TECHSPEC® Silver Off-Axis Parabolic Mirrors (OAPs) are commonly used in instrumentation and laser systems in the visible and IR spectrum, including Schlieren, MTF, FLIR, and FTIR systems. For additional surface roughness options and offset angles, please see our aluminum or gold coated OAPs or [contact us](#) for custom options.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).