

TECHSPEC[®] 50.8mm Dia., 9.53mm Thick, 532nm, λ/10 Fused Silica Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock #38-975 10 TO 12 DAYS

-

1

+

₹23,055.00

ADD TO CART

Qty 1-5
₹23,055.00
Qty 6+
₹18,444.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
45.72

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm): 532
Diameter (mm): 50.80 +0.00/-0.10
Substrate: Fused Silica (Coming 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 9.53 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Coating Specification: R_{abs} <0.25% @ 532nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 10 J/cm² @ 532nm, 20ns, 20Hz
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View