

[See all 23 Products in Family](#)

50.8 x 50.8mm Right-Handed Circular Polarizing Film (CP42HER)



Stock #29-449 **20+ In Stock**

⊖ 1 ⊕ ₹2,102

ADD TO CART

Volume Pricing	
Qty 1-5	₹2,102 each
Qty 6+	₹1,713 each
Need More?	Request Quote

Product Downloads

General

Right-Handed Circular Polarizer **Type:**

Polarization axis is parallel to marking on protective film. **Note:**

Physical & Mechanical Properties

50.80 **Length (mm):**

Dimensions (mm):

50.8 x 50.8 +0.0/-0.5

0.27 ±0.04 **Thickness (mm):**

Circular Polarizing Film **Construction:**

50.80 **Width (mm):**

Optical Properties

[Polymer Film CP42HE](#) **Substrate:**

42 **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

>99.90 **Polarization Efficiency (%):**

Environmental & Durability Factors

-40 to +80 **Operating Temperature (°C):**

80 x 500 **Heat Resistance (°C x Hours):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

Product Details

- Greater than 42% Transmission
- Available with Film or Plastic Substrate
- Right-Handed or Left-Handed Designs Available

Circular Polarizers (CP42HE and CP42HER) are ideal for reducing glare in a variety of imaging applications or for increasing the visibility of displays in bright environments. These circular polarizers feature excellent transmission of visible light from 400 – 700nm. The plastic substrate offers increased durability, while the film substrate offers increased flexibility and can be cut to fit an application's needs. Circular Polarizers (CP42HE and CP42HER) have Left-handed (CP42HE) and right-handed (CP42HER) polarization directions available. The best performance will be achieved at 560nm and polarization may become more elliptical the further the deviation from this recommended wavelength.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a Circular Polarizer (CP42HE and CP42HER) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.