

50.8mm Dia. 632.8nm λ /4 Quartz Waveplate Zero Order



Stock **#85-049** CLEARANCE 10 TO 12 DAYS

- 1 + **₹94,564.65**

ADD TO CART

Qty 1+
₹94,564.65

Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 34.00
Coating: Laser V-Coat (632.8nm)
Design Wavelength DWL (nm): 632.8
Diameter (mm): 50.80 +0.00/-0.25
Substrate: ☐ Crystal Quartz

Retardance: λ/4
Surface Quality: 10-5
Thickness (mm): 9.00 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: λ/8 for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: ±λ/200
Temperature Coefficient (λ/°C): 0.0001
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View