

[See all 7 Products in Family](#)

50.8mm Dia. x 100mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) PCX Lens | ZC-PX-50-100

See More by [ISP Optics](#)



Zinc Selenide Plano-Convex (PCX) Lenses



Stock #24-961 **CLEARANCE** 1 In Stock

- 1 + MRP ₹51,454

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹51,454 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

ZC-PX-50-100 **Model Number:**

Physical & Mechanical Properties

Physical & Mechanical Properties

50.80 +0.00/-0.13 **Diameter (mm):**

Protective as needed **Bevel:**

4.80 ±0.20 **Center Thickness CT (mm):**

<3 **Centering (arcmin):**

45.72 **Clear Aperture CA (mm):**

2.50 **Edge Thickness ET (mm):**

Optical Properties

100.00 @ 10.6µm **Effective Focal Length EFL (mm):**

Zinc Selenide (ZnSe), CVD Grade **Substrate:**

1.97 **f#:**

0.25 **Numerical Aperture NA:**

Uncoated **Coating:**

600 - 18000 **Wavelength Range (nm):**

97.78 **Back Focal Length BFL (mm):**

±2 **Focal Length Tolerance (%):**

139.96 **Radius R₁ (mm):**

60-40 **Surface Quality:**

λ/20 **Irregularity (P-V) @ 10.6µm:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 240:**

Latvia **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Low Dispersion and Absorption from 0.6 – 18µm
- High Resistance to Thermal Shock
- Uncoated or BBAR Coated for 8 – 12µm

ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are ideal for focusing or collimation of light in the Mid-Wave Infrared (MMR) and Long-Wave Infrared (LWR) spectrum. Featuring low absorption and high resistance to thermal shock, ZnSe is widely used in high power CO₂ laser systems. ZnSe is not recommended for harsh environments as it is a relatively soft material that scratches easily, and only has a Knoop Hardness of 120. ISP Optics Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are available either uncoated or Broadband Anti-Reflection (BBAR) coated for increased transmission from 8-12µm.

Note: Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

;