

[See all 18 Products in Family](#)

TECHSPEC® 50.8mm Dia., 6.35mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock **#37-690** **20+ In Stock**

MRP ₹27,544

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹27,544 each
Qty 6-25	₹24,819 each
Qty 26-49	₹21,994 each
Need More?	Request Quote

Product Downloads

General

Laser Window Substrate **Type:**

Glass **Type of Window:**

Physical & Mechanical Properties

Thickness (mm):

6.35 ±0.20

Clear Aperture CA (mm):

45.72

Diameter (mm):

50.80 +0.00/-0.10

Clear Aperture (%):

90

Parallelism (arcmin):

<3

Bevel:

Protective as needed

Edges:

Fine Ground

Optical Properties

Substrate:

Fused Silica (Corning 7980)

Index of Refraction (n_d):

1.458

Surface Quality:

10-5

Coating:

Uncoated

Abbe Number (v_d):

67.8

Wavelength Range (nm):

200 - 2200

Surface Flatness (P-V):

$\lambda/10$

Material Properties

Fused Silica Grade:

7980 0F

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Vietnam

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Up to 10-5 Surface Quality and $\lambda/10$ Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

TECHSPEC® Uncoated Laser Window Substrates are laser quality window substrates designed to be used in demanding laser applications. These laser window substrates are available, manufactured from fused silica for high power laser applications that require excellent thermal stability or from N-BK7 for more cost sensitive laser applications. Both the fused silica and N-BK7 laser window substrates feature precision grade $\lambda/10$ surface flatness and 10-5 surface quality, ensuring minimal disturbance to transmitted beams. TECHSPEC® Uncoated Laser Window Substrates are available in standard imperial sizes from 12.7 to 50.8mm in diameter for the convenience of drop-in replacement into existing laser systems. Custom dimensional and coating options are available, please contact us for custom inquiries.

Compatible Mounts

