

**TECHSPEC® 50.8mm Dia., 700 - 900nm BBAR Coated, Ultrafast Thin Window**



Stock **#11-745** 10 TO 12 DAYS

- 1 + **₹24,360.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| ₹24,360.00                    |
| Qty 6+                        |
| ₹21,924.00                    |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Abbe Number (v<sub>d</sub>):**  
67.8

**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
90

**Diameter (mm):**

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| 50.80 +0.00/-0.10                                                                                                                      |
| <b>Thickness (mm):</b><br>1.00 ±0.10                                                                                                   |
| <b>Coating:</b><br>BBAR (700-900nm)                                                                                                    |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.2% @ 700 - 900nm                                                                  |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) |
| <b>Density (g/cm³):</b><br>2.20                                                                                                        |
| <b>Design Wavelength DWL (nm):</b><br>800                                                                                              |
| <b>Edges:</b><br>Fine Ground                                                                                                           |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.458                                                                                     |
| <b>Knoop Hardness (kg/mm²):</b><br>522                                                                                                 |
| <b>Parallelism (arcsec):</b><br>≤30                                                                                                    |
| <b>Poisson's Ratio:</b><br>0.16                                                                                                        |
| <b>Substrate:</b><br><a href="#">Fused Silica</a> (Corning 7980)                                                                       |
| <b>Surface Quality:</b><br>20-10                                                                                                       |
| <b>Transmitted Wavefront, P-V:</b><br>λ/6                                                                                              |
| <b>Type:</b><br>Ultrafast Window                                                                                                       |
| <b>Wavelength Range (nm):</b><br>700 - 900                                                                                             |
| <b>Young's Modulus (GPa):</b><br>73                                                                                                    |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>10 J/cm² @ 532nm, 20ns, 20Hz                                           |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |