

50.8mm Dia, 900 - 2100nm, $\lambda/4$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-052** 10 TO 12 DAYS

-

1

+

₹271,440.00

ADD TO CART

Qty 1-5
₹271,440.00
Qty 6+
₹235,335.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): >34.0
Coating: R _{avg} <0.75% @ 900 - 2100nm
Diameter (mm): 50.80
Substrate: ☐

Crystal Quartz and MgF ₂
Retardance: λ/4
Surface Quality: 40-20
Thickness (mm): 6.00 ±0.2
Type: Achromatic Waveplate
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/4 @ 632nm
Parallelism (arcsec): <10
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: λ/100 @ 20°C
Coating Specification: R _{avg} <0.75% @ 900 - 2100nm
Wavelength Range (nm): 900 - 2100
Damage Threshold, By Design: ☐ >5 J/cm ² @ 1064nm, 10ns, 10Hz
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant