


[See all 11 Products in Family](#)

**TECHSPEC® 50.8mm Dia. NIR, Precision Broadband Laser Mirror**



Stock #75-421 **NEW** 6 In Stock

⊖ 1 ⊕ ₹28,275

**ADD TO CART**

Volume Pricing	
Qty 1+	₹28,275 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**  
Optical Power: X10 **Note:**

**Physical & Mechanical Properties**

>90 **Clear Aperture (%):**  
Ground **Back Surface:**  
Diameter (mm):

50.80 0.0/-0.1

Thickness (mm):

12.50 ±0.2

## Optical Properties

Surface Quality:

20-10

Coating Specification:

R<sub>avg</sub> >99% @ 700 - 900nm

Wavelength Range (nm):

700 - 900

Irregularity (P-V) @ 632.8nm:

λ/20

Coating Type:

Dielectric

Coating:

Dielectric Mirror (700-900nm)

Angle of Incidence (°):

0-45

Substrate:

[Fused Silica](#) (Corning 7980)

Damage Threshold, By Design:

20 J/cm<sup>2</sup> @ 10ns @ 800nm

## Environmental & Durability Factors

Durability:

ML-PRF-13830B

## Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Tunable Lasers and Reflecting Multiple Laser Sources
- High Reflectivity from 0 - 45° for All Polarization States
- Variety of Coating Options Available


TECHSPEC® Precision Broadband Laser Mirrors feature high reflectivity and are ideal for UV, visible, and NIR beam steering applications. The broadband dielectric enhanced silver coatings feature >98% reflectivity from 450nm to 12µm wavelengths at incident angles from 0 - 45°. These mirrors meet ML-M-13508-C durability standards. [TECHSPEC® Precision Broadband Laser Mirrors](#) are ideal for demanding laser applications requiring high laser damage thresholds including laser scanning and beam steering. The mirrors have a BOROFLOAT® substrate, and are offered in 12.70, 25.40, and 50.80mm diameters.

**LASER OPTICS** MADE BY EDMUND OPTICS®


[LEARN MORE](#)

## Technical Information


**Mirror for Visible Laser**



**Silver AOI=45°**



**Mirror for UV 300-500nm**



**Mirror for Near-IR**

