

[See all 47 Products in Family](#)

TECHSPEC® 50.8mm Dia. x 2mm Thickness 3-5µm Coated Silicon Window



TECHSPEC Silicon (Si) Windows

Stock **#20-040** CLEARANCE **5 In Stock**

MRP ₹43,988

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹43,988 each
Qty 11-25	₹38,742 each
Qty 26-49	₹36,724 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

45.72	
50.80 +0.0/-0.1	Diameter (mm):
2.00 ±0.1	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
90.00	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
140	Young's Modulus (GPa):
1,150.00	Knoop Hardness (kg/mm²):

Optical Properties

BBAR (3000-5000nm)	Coating:
Silicon (Si)	Substrate: <input type="checkbox"/>
3.422 @ 5µm	Index of Refraction (n_d):
60-40	Surface Quality:
R _{avg} <3.0% @ 3 - 5µm	Coating Specification:
3000 - 5000	Wavelength Range (nm):
1.5λ	Surface Flatness (P-V):

Material Properties

2.33	Density (g/cm³):
2.55	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume





Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Transmission from 1.2 - 7µm
- Available Uncoated or AR Coated for 1.65 - 5µm
- Ideal for Weight Sensitive Applications

TECHSPEC® Silicon (Si) Windows manufactured from optical grade silicon are popular for the 1.2 - 7 μ m spectral region due to their low cost and low density. Due to its low density (half that of [germanium](#) or [zinc selenide](#)), silicon is ideal for weight sensitive applications, especially those in the 1.65 - 5 μ m region. Density is 2.329 g/cm³ and Knoop Hardness is 1150, making it harder and less brittle than germanium. TECHSPEC® Silicon (Si) Windows available uncoated or AR coated for 1.65 - 5 μ m. These crystal windows are offered in diameters ranging from 10 – 76.20mm.

Technical Information



Compatible Mounts