

TECHSPEC[®] 50.8mm Dia. x 76.2mm EFL, Enhanced Aluminum 50Å 90° Off-Axis Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#37-993** 10 TO 12 DAYS

[Other Coating Options](#)

-

1

+

₹39,150.00

ADD TO CART

Qty 1-5

₹39,150.00

Qty 6+

₹35,235.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
50.80 +0.0/-0.1

Effective Focal Length EFL (mm):
76.20

Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 76.20
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 38.1
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 250 - 700
Surface Quality: 80-50
Compatible Mounting Plates: #47-112
Substrate: Aluminum 6061-T6
Y Offset (mm): 76.20
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View