

[See all 32 Products in Family](#)

**TECHSPEC® 50.8mm Dia. x 9.53mm 532/630-655/1064nm, 0-45° AOI, Dual Band Laser Mirror**



Stock #28-982 **9 In Stock**

- 1 + MRP ₹41,365

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹41,365 each
Qty 6-25	₹36,320 each
Qty 26+	₹35,160 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

Commercial Polish	<b>Back Surface:</b>
50.80 +0.00/-0.10	<b>Diameter (mm):</b>
9.53 ±0.20	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
10-5	<b>Surface Quality:</b>
99.5	<b>Reflection at DWL (%):</b>
<b>Coating Specification:</b> R <sub>avg</sub> ≥ 99.50% @ 532nm & 1064nm @ 0-45° AOI R <sub>avg</sub> ≥ 80% @ 630 – 655nm @ 0-45° AOI	
λ/10	<b>Surface Flatness (P-V):</b>
Dielectric	<b>Coating Type:</b>
Laser Mirror (532, 635, 650, 1064nm)	<b>Coating:</b>
532, 635, 650, 1064	<b>Design Wavelength DWL (nm):</b>
0 - 45	<b>Angle of Incidence (°):</b>
<b>Fused Silica</b> (Coming 7980)	<b>Substrate:</b> <input type="checkbox"/>
Not Specified	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.