

TECHSPEC®

50mm Dia., 0.66 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#16-969-INK** 17 TO 22 D=DAYS

[Other Coating Options](#)

⊖ 1 ⊕

₹54,810.00

ADD TO CART

Qty 1-5
₹54,810.00
Qty 6+
₹43,848.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
37.50 @ 587.6nm

Numerical Aperture NA: 0.66
Back Focal Length BFL (mm): 24.74
Substrate: N-SF5
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: VIS-EXT+ (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 45.00
Edge Thickness ET (mm): 7.47
Center Thickness CT (mm): 21.34 ±0.10
f#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View