

[See all 31 Products in Family](#)

TECHSPEC[®] 50mm Dia. x 100mm FL 1550nm V-Coat, UV PCX Lens



Stock **#34-171** **3 In Stock**

☐ [Other Coating Options](#)

-

1

+

₹24,056

ADD TO CART

Volume Pricing	
Qty 1-5	₹24,056 each
Qty 6-25	₹19,229 each
Qty 26-49	₹18,061 each
Need More?	Request Quote

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

50.00 +0.0/-0.025

≤1	Centering (arcmin):
9.00 ±0.10	Center Thickness CT (mm):
1.58	Edge Thickness ET (mm):
49.00	Clear Aperture CA (mm):
Protective as needed	Bevel:
Fine Ground, Protective Bevel as Needed	Edges:

Optical Properties	
100.00 @587.6nm	Effective Focal Length EFL (mm):
93.84	Back Focal Length BFL (mm):
Laser V-Coat (1550nm)	Coating:
R _{abs} <0.25% @ 1550nm	Coating Specification:
Fused Silica (Corning 7980)	Substrate: □
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
45.85	Radius R ₁ (mm):
2.00	f##:
0.25	Numerical Aperture NA:
587.6	Design Wavelength DWL (nm):
5 J/cm² @ 1550nm, 10ns	Damage Threshold, By Design: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- <0.25% Reflection at 1550nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [633nm](#), and [1064nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

• Scalable production—from prototype to volume
Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
