


[See all 22 Products in Family](#)

50mm Dia., 80° Diffusion Angle, High Efficiency Diffuser



HE Single Sided Diffuser

Stock **#70-768** 20+ In Stock

-

1

+

₹6,968

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,968 each
Qty 10-25	₹4,878 each
Qty 26-49	₹4,529 each
Need More?	Request Quote

Product Downloads





General	
High Efficiency Diffuser	Type:
Physical & Mechanical Properties	
50.00 ±0.13	Diameter (mm):
1.59 +/-0.16	Thickness (mm):

Optical Properties	
80	Diffusing Angle (°):
PMMA	Substrate: ☐
Environmental & Durability Factors	
-34 to +70	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Efficiency, Angle Bending, Batwing, and Elliptical Configurations Available
 - Transmission Efficiency >88%
 - Low-Cost, High-Performance Diffusers
- Beam Shaping Diffusers provide an even distribution of LED and fluorescent illumination in a variety of configurations including High Efficiency, Angle Bending, Batwing, and Elliptical while maintaining a high transmission efficiency of >88%. The high efficiency and angle bending configurations provide even light distribution whereas the batwing and elliptical configurations distribute light according to their respective geometries. Beam Shaping Diffusers feature diffusing angles between 8° - 127° and are available as 25mm diameter unmounted optics with a thickness of no more than 1.75mm, enabling easy integration into a variety of bench top or OEM applications. These Diffusers are ideal for applications where excellent depixelation, angle control, color mixing, and color uniformity are required.

Technical Information

BEAM SHAPING DIFFUSERS		
Type of Diffuser	Description	Diffusion Example
High Efficiency Diffuser	High Efficiency Diffusers are ideal for providing even illumination in LED applications. They provide excellent depixelation, angle control, and color uniformity.	 
Linear Batwing Diffuser	Linear Batwing Diffusers diffuse light in a batwing distribution, ideal for eliminating central hotspots from a light source. Incident light should be from the glossy, specularly-reflective side of these diffusers for optimal performance. Light distributions may vary significantly depending on the light source used.	 
Elliptical Diffuser	Elliptical Diffusers diffuse light assymmetrically, creating an elliptical light pattern. The diffusing angles are specified as W x L.	 
Angle Bending Diffuser	Angle Bending Diffusers both redirect and diffuse incident light, ideal for creating diffuse lighting in space-constrained environments.	